

5mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#27-400** 10 TO 12 DAYS

-

1

+

₹1,044.00

ADD TO CART

Qty 1-5
₹1,044.00
Qty 6+
₹870.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 5.00 ±0.76
Surface Flatness (P-V): 4 - 6λ
Substrate: Float Glass
Surface Quality:

80-50
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Thickness (mm): 1.00 Nominal
Thickness Tolerance (mm): Nominal
Type: Flat Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant