

5mW, 30° Gaussian Line, Harsh Environment Green Diode



Stock **#63-875** 10 TO 12 DAYS

-

1

+

₹62,205.00

ADD TO CART

Qty 1+
₹62,205.00
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
0 to +35

Output Power (mW):
5

Power Stability (%):
±5%

Dimensions (mm): 20 Dia. x 136 L
Wavelength (nm): 532.00
Weight (g): 87.00
Laser Class - IEC: 2M
Housing Length (mm): 136.00
Housing Diameter (mm): 20.00
Storage Temperature (°C): -10 to +80
Mean Time To Failures MTTF @ 25° (hours): >10,000
Beam Diameter (mm): 5.00
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): <1 without Line Optics
Laser Class - CDRH: IIIa
Color: Green
Connector: 4 Pins, M12
Fan Angle (°): 30.00
Focus Range: 200mm to Collimation
Input Voltage (V): 5 - 30 DC

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View