

# 5mW, 532nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock **#37-027** 10 TO 12 DAYS

- 1 +

₹29,798.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹29,798.00                    |
| Qty 10+                       |
| ₹26,796.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Operating Temperature (°C):  
23 to 27

Operating Voltage (V):  
5.0

Output Power (mW):  
5

Spatial Mode:

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| TEM <sub>00</sub>                                                                                                                                                                                                                           |
| <b>Wavelength (nm):</b><br>532.00 ±1                                                                                                                                                                                                        |
| <b>Wavelength Tolerance (nm):</b><br>±1                                                                                                                                                                                                     |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#83-855</a><br>Europe: <a href="#">#83-855</a><br>Japan: <a href="#">#13-640</a><br>Korea: <a href="#">#33-770</a><br>China: <a href="#">#83-855</a> |
| <b>Modulation Frequency (kHz):</b><br>0 - 10                                                                                                                                                                                                |
| <b>Note:</b><br>Compatible TEC Controller <a href="#">(#19-476)</a> sold separately                                                                                                                                                         |
| <b>Beam Diameter (mm):</b><br>1.0 Typical                                                                                                                                                                                                   |
| <b>Beam Divergence (mrad):</b><br><1 Typical                                                                                                                                                                                                |
| <b>Laser Class - CDRH:</b><br>IIIb                                                                                                                                                                                                          |
| <b>Color:</b><br>Green                                                                                                                                                                                                                      |
| <b>Length (mm):</b><br>90.00                                                                                                                                                                                                                |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |