

TECHSPEC® 6" Diameter x 24" FL Enhanced Aluminum, Parabolic Mirror



Stock **#32-069-533** 10 TO 12 DAYS

- 1 + **₹65,772.00**

ADD TO CART

Qty 1-4
₹65,772.00
Qty 5+
₹55,941.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: 

Focal Length Tolerance (%):
±1

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 6.0 +0.06/-0
Diameter (mm): 152.40 +1.5/-0
Effective Focal Length EFL (inches): 24.0
Effective Focal Length EFL (mm): 609.60
Radius of Curvature (mm): 1,219.20
Aperture (f/#): f/4
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 138
Edge Thickness ET (inches): 1.00
Edge Thickness ET (mm): 25.40
Type: Parabolic Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference:  0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant