


6 x 6 x 1mm, 800nm SHG, Type I BBO Nonlinear Crystal



Mounted Type I BBO Nonlinear Crystal

Stock **#15-277** 10 TO 12 DAYS



1



₹49,590.00

ADD TO CART

Qty 1-2
₹49,590.00
Qty 3+
₹43,935.00
Volume Pricing
Request Quote

Get Product Downloads

Crystal Type: BBO
Design Wavelength DWL (nm): 800
Clear Aperture CA (mm): 5.70
Dimensions (mm):

6.0 x6.0 +0.0/-0.1
Thickness (mm): 1.00 +0.0/-0.1
Protective Chamfer: <0.1mm x45°
Orientation Θ/Φ (°): 29.2/90
Coating: AR Coating
Coating Specification: S1 & S2: R _{avg} <3% @400 - 800nm
Parallelism (arcsec): <20
Perpendicularity (arcmin): <5
Surface Quality: 20-10
Surface Flatness (P-V): λ/8
Mount: Mounted
Mount Diameter (mm): 25.4
Mount Thickness (mm): 6 (unthreaded)
Typical Applications: SHG @ 800nm, Type I
Type: Nonlinear Crystal
Damage Threshold, By Design: ☐ 10 J/cm ² @ 1064nm, 10ns, 10Hz
Note: Mount is 25.4mm Dia., 6mm Thick Unthreaded Black Anodized Metal Mount (see drawing for more information)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant