

[See all 62 Products in Family](#)

Coherent® StingRay™ Projection Head 1254120 | 514nm, 60° Fan

See More by [Coherent®](#)



60° Line, 514nm Stingray Projection Head, #89-579

Stock **#89-579** **1 In Stock**

MRP ₹36,942

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹36,942 each
Need More?	Request Quote

Product Downloads



General

1 Line **Type:**

Compatible Laser Models:
[86-848, 87-522](#)

Manufacturer:
Coherent®

Optical Properties

Wavelength (nm):

514.00

Green

Color:

60.00

Fan Angle (°):

Regulatory Compliance

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

Singapore

Country of Origin:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Imported By:

Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5□5V) with BNC connector is required.