

Richardson Gratings™ 600 Grooves, 12.5 x 12.5mm, 1850nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #37-123 10 TO 12 DAYS

- 1 + ₹11,397.00

ADD TO CART

Qty 1+
₹11,397.00

Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
600

Wavelength Range (nm):
1000 - 2400

Blaze Wavelength (nm): 1850 ±25
Blaze Angle (°): 34
Peak Efficiency, Typical (%): 91
Dimensions (mm): 12.5 x 12.5 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 12.50
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.50
Reflected Wavefront, RMS: $\lambda/4$
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S and P
Master Reference: 0951
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View