

TECHSPEC® 6.0mm Dia. x 18.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock **#47-464-INK** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹4,089.00**

ADD TO CART

Qty 1-9
₹4,089.00
Qty 10+
₹3,676.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):
18.00 @ 587.6nm

Back Focal Length BFL (mm): 17.07
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.42 ±0.05
Edge Thickness ET (mm): 0.90
Radius R₁ (mm): 9.30
Clear Aperture CA (mm): 5.4
f/#: 3
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View