

60X DIN Achromatic Finite Intl Standard Objective



Stock #33-440 10 TO 12 DAYS

⊖ 1 ⊕ ₹13,920.00

ADD TO CART

Qty 1+
₹13,920.00

Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
546

Field of View (mm):
0.33

Focal Length FL (mm):
2.70

Length excluding Threads (mm):
44.70

Magnification:
60X

Maximum Diameter (mm): 25
Numerical Aperture NA: 0.85
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 160mm
Type: Achromatic
Depth of Field (µm): 1.01
Field of View, 18 Diameter Field Eyepiece (mm): 0.30
Operating Temperature (°C): +10 to +40
Operating Humidity: Max 85% at 35°C with no condensation
Working Distance (mm): 0.15
Weight (g): 74.2
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Field Number (mm): 20
Parfocal Length (mm): 44.85
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View