

630nm LED Area Light



Stock #63-308 10 TO 12 DAYS

-

1

+

₹58,725.00

ADD TO CART

Qty 1+
₹58,725.00

Volume Pricing
Request Quote

Get Product Downloads

Color: Red
Diameter (mm): 35.00
Full Width-Half Max FWHM (nm): 30.00
Height (mm): 29.5
Wavelength (nm): 630.00

Divergence Angle (°): ±9.2
LED Lifetime (hours): 100,000
Power Supply: Power Supply Required and Sold Separately: USA: #59-433 Europe: Not Available Japan: #59-433 Korea: Not Available China: #59-433
Spot Size at 100mm Working Distance (mm): 45.00
Irradiance at 100mm (W/m²): 228.00
Type of Illumination: LED Illuminator
Geometry: Area Light
Illumination Mode: Strobed or Constant

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
