

TECHSPEC[®] 6.35mm Dia Enhanced Aluminum, 4-6λ Mirror



Stock #45-610 10 TO 12 DAYS

-

1

+

₹2,088.00

ADD TO CART

Qty 1-5
₹2,088.00
Qty 6+
₹1,610.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.35 ±0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} ≥95% @450 - 650nm @45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 5.35
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Damage Threshold, By Design: ☐ 0.2 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant