

TECHSPEC® 6.35mm Dia Silver, 4-6λ Mirror



Stock **#89-466** 10 TO 12 DAYS

- 1 +

₹2,436.00

ADD TO CART

Qty 1-5
₹2,436.00
Qty 6+
₹1,871.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.35 ±0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 5.35
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant