

6.37mm FL, No IR-Cut Filter, f/2.4, Micro Video Lens



Stock **#55-573** 10 TO 12 DAYS

[Similar Products](#)

- 1 + **₹5,220.00**

ADD TO CART

Qty 1-49
₹5,220.00
Qty 50+
₹4,089.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
13.12

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
14.8

Maximum Image Circle (mm):

6.00
Horizontal Field of View @ Max Sensor Format: 42.2
Resolution, On-Axis: 80 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 63 lp/mm @ 20% Contrast
Resolution, Full Field: 25 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 6.40
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2.4
Distortion (%): -2.40 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View