

7" Diagonal LCD Flat Panel Monitor



Stock **#35-128** CLEARANCE CONTACT US

-

1

+

₹9,000

ADD TO CART

Qty 1+

₹9,000

Volume Pricing

[Request Quote](#)

Product Downloads

SPECIFICATIONS

General

	Type:
Monitor	
	Size of Screen, Diagonal (inches):
6.4	
	Maximum Viewing Angle, MVA (°):
Left/Right/Down 70, Up 50	

400	Brightness (cd/m²):
Tr: 12ms Tf: 18ms	Response Time (ms):
FCC Class B	Safety Standards:
Physical & Mechanical Properties	
179.6 x 120 x 23	Dimensions (mm):
870	Weight (g):
0.135 x 0.416	Dot Pitch (mm):
154.08 x 86.58	Active Area (mm):
Optical Properties	
1440 x 234	Resolution:
Sensor	
0.50	Resolution (MegaPixels):
NTSC/PAL	Signal Format:
400:1 (typical)	Contrast:
Electrical	
7.5	Power Consumption (W):
Hardware & Interface Connectivity	
100 - 240 V AC Included	Power Supply:
Mini Phone Jack (RCAAdapter Included)	Input/Output Options:
NTSC/PAL	Video Input:
Regulatory Compliance	
Compliant	RoHS:
View	Certificate of Conformance:

PRODUCT DETAILS

- Multiple Sizes
- Cost Effective
- Fast Response Time

LCD monitors are very popular because of their great space saving advantages as opposed to the bulkyshape of a CRT monitor. The monitor's can be connected to any of our color or monochrome analog CCD cameras via connecting [video cable](#).

All input connections on the 15.1" monitor are accessible via a removable back panel. One of the many OSD (on screen display) features of the 15.1" monitor is an automatic adjustment function that adjusts the size, position, and phase optimally according to the applied video signal. Power supply and tip/tilt mount included.