

TECHSPEC[®] 6° Nom. 12.5mm Dia. VIS 0°, N-BK7 Wedge Prism



Stock #35-789 10 TO 12 DAYS

-

1

+

₹4,133.00

ADD TO CART

Qty 1-5
₹4,133.00
Qty 6+
₹3,306.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
VIS 0° (425-675nm)

Angle Tolerance (arcsec):
±30

Bevel:
Protective bevel as needed

Coating Specification:

R _{avg} ≤0.4% @ 425 - 675nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 12.50 +0.00/-0.10
Edge Thickness ET (mm): 1.5
Image Orientation: Beam Deviation
Power (diopters): 10.51
Ray Deviation @ 633nm (°): 6.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Type: Wedge Prism
Wavelength Range (nm): 425 - 675
Wedge Angle: 11° 21'

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant