

TECHSPEC[®] 6mm Diameter x -6 FL, VIS 0°, Inked, Plano-Concave Lens



Stock **#48-265-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹4,263.00

ADD TO CART

Qty 1-9
₹4,263.00
Qty 10+
₹3,828.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):
-6.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: VS 0° (425-675nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -6.84
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.4
Coating Specification: R_{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 2.22
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -4.71
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View