

TECHSPEC® 6" Dia. Protected Silver, λ /20 Flat Fused Silica



Stock #47-575-577 10 TO 12 DAYS

- 1 + **₹247,428.00**

ADD TO CART

Qty 1-5
₹247,428.00
Qty 6+
₹222,720.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 λ /20 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 152.40 +0.0/-1.02
Diameter Tolerance (inches): +0.0/-0.04
Substrate: Fused Silica (Corning 7980)
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 137.16
Note: Flatness is specified as Peak to Valley
Thickness (mm): 25.40 ±2.0
Thickness Tolerance (mm): ±2.0
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: 0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant