

700nm CWL, 80nm FWHM, 50mm Mounted Diameter



Stock #87-194 10 TO 12 DAYS

[Additional Bandwidths](#)



1



₹38,628.00

ADD TO CART

Qty 1-9
₹38,628.00
Qty 10+
₹34,713.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm): 42.0
Center Wavelength CWL (nm): 700.00 ±15
Center Wavelength CWL Tolerance (nm): ±15
Full Width-Half Max FWHM (nm): 80.00 ±25
Full Width-Half Max FWHM Tolerance (nm): ±25
Minimum Transmission (%): ≥60
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Clinical Chemistry
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View