

50mm Max. Aperture, Iris Diaphragm



Stock #32-617 10 TO 12 DAYS

- 1 + ₹11,745.00

ADD TO CART

Qty 1-4
₹11,745.00
Qty 5+
₹10,405.00
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
2.5

Maximum Aperture (mm):
50.0

Outer Diameter (mm):
70.0

Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 15.00
Number of Leaves: 16.00
Thickness (mm): 7.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)