

50mm Max. Aperture, Stainless Steel Iris Diaphragm



Stock #53-913

CONTACT US

-

1

+

₹16,008.00

ADD TO CART

Qty 1-4
₹16,008.00
Qty 5+
₹14,164.00
Volume Pricing
Request Quote

Get Product Downloads

Type:

Unmounted

Minimum Aperture (mm):

2.8

Maximum Aperture (mm):

50.0

Outer Diameter (mm):

70.0

Construction: Blackened Brass Housing, Stainless Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 15.00
Number of Leaves: 16.00
Thickness (mm): 7.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)