

70mm Sq. English Kinematic Magnetic Base



Stock #22-405 **2 In Stock**

⊖ 1 ⊕ ₹10,269

ADD TO CART

Volume Pricing

Qty 1-9	₹10,269 each
Qty 10+	₹9,286 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

No **Switchable:**

Physical & Mechanical Properties

25.40 **Thickness (mm):**

70.00 **Width (mm):**

0.27 **Weight (kg):**

Anodized Aluminum **Construction:**

70.00 **Length (mm):**

<70.0 **Repeatability (µrad):**

Threading & Mounting

(8) 8-32, (11) 1/4-20 **Mounting Threads:**

Material Properties

20 **Magnetic Force (N):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Taiwan **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.