

TECHSPEC® 70R/30T 30mm Dia., UV Plate Beamsplitter



TECHSPEC® UV Plate Beamsplitters

Stock **#84-489** 10 TO 12 DAYS

- 1 + **₹13,224.00**

ADD TO CART

Qty 1-5
₹13,224.00
Qty 6+
₹10,571.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: R_{abs} = 70 ±5% @ 350nm, R_{avg} = 70 ±10%
over 250 - 450nm

T _{abs} =30 ±5% @ 350nm, T _{avg} = 30 ±10% over 250 - 450nm Surface 2: BBAR (R _{avg} <1%, R _{abs} <2% over 250 - 450nm)
Construction: Plate
Diameter (mm): 30.00
Dimensional Tolerance (mm): +0.0/-0.2
Parallelism (arcmin): <5
Reflection/Transmission Ratio (R/T): 70/30
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.38
Type: Standard Beamsplitter
Wavelength Range (nm): 250 - 450

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant