

TECHSPEC[®] 75/76.2mm Blank Table: No Holes



Stock #58-863 10 TO 12 DAYS

-

1

+

₹9,570.00

ADD TO CART

Qty 1-4
₹9,570.00
Qty 5+
₹8,648.00
Volume Pricing
Request Quote

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Square or Rectangular

Size of Compatible Optics (mm):
3.0 - 76.2

Number of Adjustment Screws: 2
Thickness of Front Plate to C'bore (mm): 45.6
Travel (mm): No Z-Axis Translation
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.2 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 2.3
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Compatible Post: M4 x0.7, 8-32
Thickness of Front Plate to Back Plate (mm): 28.4
Pointing Stability (μrad): 1.3
Plate Size (mm): 76.2 x 76.2
Plate Type: Solid Plate (No Hole)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View