

TECHSPEC® 75mm Dia. Linear Plastic Polarizer (XP42-200)



Stock **#85-923** 10 TO 12 DAYS

- 1 + **₹4,872.00**

ADD TO CART

Qty 1-5
₹4,872.00
Qty 6+
₹3,828.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
75.00 +0.0/-0.3

Extinction Ratio:
9000:1

Substrate: ☐
[XP42-200 on PMMA](#)

Operating Temperature (°C):
-40 to +80

Thickness (mm): 2.22 ±0.25
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004
Type: Linear Polarizer
Construction: Polarizing Film on PMMA
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant