

75mm Focal Length Lens, 1" Sensor Format



75mm Focal Length Lens, 1" Sensor Format, #63-249

Stock **#63-249** 10 TO 12 DAYS

-

1

+

₹60,900.00

ADD TO CART

Qty 1+
₹60,900.00

Volume Pricing
Request Quote

Get Product Downloads

Iris Option:
Variable

Length (mm):
57.00

Filter Thread:
M46 x0.75

Maximum Diameter (mm):
48.0

Weight (g):
180

Horizontal Field of View, 1" Sensor: 9.7°
Maximum Image Circle (mm): 16.00
TV Distortion (%): <0.2
Type: Fixed Focal Length Lens
Focal Length FL (mm): 75.00
Maximum Sensor Format: 1"
Working Distance (mm): 1,000 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/16
Maximum Distortion (%): < -0.2%
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)