

TECHSPEC® 8" Diameter x 64" FL Uncoated, Parabolic Mirror



Stock #32-075-000 [CONTACT US](#)

- 1 + **₹73,341.00**

ADD TO CART

Qty 1-2
₹73,341.00
Qty 3+
₹62,379.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 8.0 +0.06/-0
Diameter (mm): 203.20 +1.5/-0
Effective Focal Length EFL (inches): 64.0
Effective Focal Length EFL (mm): 1,625.60
Radius of Curvature (mm): 3,251.20
Aperture (f/#): f/8
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 183
Edge Thickness ET (inches): 1.37
Edge Thickness ET (mm): 34.80
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View