

8-pin GPIO Y-cable, IP65/67, 5m

See More by [IDS Imaging Development Systems](#)



Stock **#19-691** [CONTACT US](#)

-

1

+

₹14,000

ADD TO CART

Volume Pricing	
Qty 1+	₹14,000 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Camera Accessory

Type:

Note:
8-pin Binder Connector to open end, 2 branches:
one branch 6 wires for Trigger and Flash (5m), one
branch 2 wires for power (5m)

Hardware & Interface Connectivity

5, 5	Length of Cable (m):
8-pin Binder Connector	Connector:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.