

8", Red 625nm, Medium Intensity Linear Backlights

See More by [Advanced Illumination](#)



Advanced Illumination Medium Intensity Linear Backlights

Stock **#18-641** 10 TO 12 DAYS

- 1 +

₹70,905.00

ADD TO CART

Qty 1+
₹70,905.00

Volume Pricing
Request Quote

Get Product Downloads

Color: Red
Input Voltage (V): 24V
Model Number: BL31308-625
Operating Temperature (°C): 0 - 50
Dimensions (mm):

216.4 x 32.2 x 21.7
Wavelength (nm): 625.00
Weight (g): 263
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (mm): 204.4 x 25
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant
Environmental Rating: IP50
Minimum Input Current: 0.8A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)