

80° Diffusing Angle 12.5mm Unmounted



Stock #35-870

10 TO 12 DAYS



1



₹7,830.00

ADD TO CART

Qty 1-5

₹7,830.00

Qty 6+

₹5,873.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (°):

±8

Diffusing Angle (°):

80 (FWHM)

Diameter (mm):

12.50

Dimensional Tolerance (mm):

±0.5

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant