

60mm Max. Aperture, Burnished Steel Leaves Iris Diaphragm



Standard Series

Stock **#57-585** 10 TO 12 DAYS

⊖ 1 ⊕

₹17,661.00

ADD TO CART

Qty 1-4
₹17,661.00
Qty 5+
₹15,573.00
Volume Pricing
Request Quote

Get Product Downloads

Type: Unmounted
Minimum Aperture (mm): 4.0, Typical
Maximum Aperture (mm): 60.0
Outer Diameter (mm):

82.0
Construction: Anodized Aluminum Alloy, Burnished Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.00
Number of Leaves: 17.00
Thickness (mm): 8.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant