

830 Grooves, 12.7mm Sq, 29.9° Groove Angle Grating



Stock #49-577

10 TO 12 DAYS

-

1

+

₹8,700.00

ADD TO CART

Qty 1-9
₹8,700.00
Qty 10+
₹7,830.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):

830

Wavelength Range (nm):

400 - 700

Blaze Angle (°):

29.9

Dimensions (mm): 12.70 x 12.70
Construction: Blazed (Ruled) Grating
Length (mm): 12.70
Substrate: ☐ B270
Thickness (mm): 3.00 ±0.5
Type: Transmission Diffraction Grating
Wavelength: VIS
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5
Groove Angle (°): 29.9

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
