

[See all 5 Products in Family](#)

850nm, UltraSeal Washdown Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity UltraSeal Washdown Spot Lights

Stock **#21-974** CLEARANCE **1 In Stock**

-

1

+

₹1,02,743

ADD TO CART

Volume Pricing	
Qty 1+	₹1,02,743 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
SL316M-850IC	Model Number:
50,000	LED Lifetime (hours):
25	Number of LEDs:
LED Illuminator	Type of Illumination:

Advanced Illumination	Manufacturer:
Spot Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
290	Weight (g):
Optical Properties	
IR	Color:
850	Wavelength (nm):
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Power Supply:
2	Length of Cable (m):
Environmental & Durability Factors	
0 to +60	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- IP69K Certified for Extreme Washdown Environments
- Ideal for Hygienic and Aseptic Manufacturing Applications
- Intensity of Over 60,000 Lux at 300mm Working Distance

Advanced Illumination High Intensity UltraSeal Washdown Spot Lights are ideal for extreme environments including high pressure steam cleaning and prolonged liquid immersion. Available in five colors, these spot lights feature high intensity output and consistent uniformity. These spot lights are IP69K certified and their proprietary nickel finish ensures better thermal conductivity than stainless steel while the sealed design reduces the potential for material buildup and improves cleanability. Advanced Illumination High Intensity UltraSeal Washdown Spot Lights can be used in hygienic inspection environments, aseptic manufacturing, and food and beverage applications.