

50mm Max. Aperture, Mounted Stainless Steel Iris Diaphragm



Stock #62-660 10 TO 12 DAYS

- 1 + ₹22,707.00

ADD TO CART

Qty 1-4
₹22,707.00
Qty 5+
₹20,027.00
Volume Pricing
Request Quote

Get Product Downloads

Type: Mounted
Minimum Aperture (mm): 2.8
Maximum Aperture (mm): 50.0
Outer Diameter (mm): 86.0

Construction: Blackened Brass Housing, Stainless Steel Leaves, Stainless Steel Pin Actuators
Lever Diameter (mm): 3.00
Lever Length (mm): 15.00
Number of Leaves: 16.00
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)