

TECHSPEC® 8° Nom. Uncoated, N-BK7 Wedge Prism



Stock #45-401 10 TO 12 DAYS

- 1 + **₹4,133.00**

ADD TO CART

Qty 1-5
₹4,133.00
Qty 6+
₹3,306.00
Volume Pricing
Request Quote

Get Product Downloads



Coating: Uncoated
Angle Tolerance (arcsec): ±30
Bevel: Protective bevel as needed
Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 25.00 +0.00/-0.10
Image Orientation: Beam Deviation
Power (diopters): 14.05
Ray Deviation @ 633nm (°): 8.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Type: Wedge Prism
Wavelength Range (nm): 350 - 2200
Wedge Angle: 14° 51'
Maximum Edge Thickness (mm): 9.6

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View