

TECHSPEC® 8mm Aperture x 100mm L Standard NA, Fused Silica Light Pipe



Fused Silica Light Pipe Homogenizing Rods



Stock **#63-096** 10 TO 12 DAYS

- 1 + **₹19,575.00**

ADD TO CART

Qty 1-5
₹19,575.00
Qty 6+
₹15,660.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Substrate:
[Fused Silica](#) (Corning 7980)

Length (mm): 100.00
Surface Quality: 60-40
Type: Light Pipe
Entrance and Exit Aperture (mm): 8.00
Parallelism (arcmin): 5.00
Length Tolerance (mm): ±0.3
Aperture Tolerance (mm): ±0.10
Image Orientation: Light Homogenization
Light Source NA: Standard
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): 3λ
#Sorting: 49.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View