

9 x 9mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #31-004 7 DAYS

-

1

+

₹1,305.00

ADD TO CART

Qty 1-5

₹1,305.00

Qty 6+

₹1,044.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm):

9.0 x 9.0 ±0.76
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 1.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 9.00
Width (mm): 9.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant