

TECHSPEC® 9.0mm Dia. x 13.5mm FL Uncoated, Plano-Convex Lens



Stock **#32-009** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹2,436.00**

ADD TO CART

Qty 1-9
₹2,436.00
Qty 10+
₹2,197.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
13.50 @ 587.6nm

Back Focal Length BFL (mm): 11.94
Coating: Uncoated
Substrate: 
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.60 ±0.05
Edge Thickness ET (mm): 1.41
Radius R₁ (mm): 9.09
Clear Aperture CA (mm): 8.1
f#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 380 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View