

TECHSPEC[®] 9.0mm Dia. x 20mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock #38-441-INK 17 TO 22 D= DAYS

[Other Coating Options](#)

-

1

+

₹4,394.00

ADD TO CART

Qty 1-9

₹4,394.00

Qty 10+

₹3,959.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 ±0.025

Effective Focal Length EFL (mm):
20.00 @ 587.6nm

Back Focal Length BFL (mm): 18.55
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.20 ±0.05
Edge Thickness ET (mm): 1.17
Radius R₁ (mm): 10.34
Clear Aperture CA (mm): 8.1
f/#: 2.22
Numerical Aperture NA: 0.23
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View