

94mm Outer Dia., Zero Aperture, Stainless Steel Leaves



Zero Series

Stock **#57-599** 10 TO 12 DAYS

-

1

+

₹21,141.00

ADD TO CART

Qty 1-4
₹21,141.00
Qty 5+
₹18,705.00
Volume Pricing
Request Quote

Get Product Downloads
Minimum Aperture (mm): 0.00
Maximum Aperture (mm): 60.0
Outer Diameter (mm): 94.0
Construction:

Anodized Aluminum Alloy, Stainless Steel Leaves
Full Angular Range of Lever (°): 98.00
Lever Length (mm): 25.00
Lever Position (mm): 4.50
Lever Size (mm): 14.00 x 2.00
Number of Leaves: Two sets of 8
Operating Temperature (°C): <400
Pin Thread & Pitch: N/A
Thickness (mm): 9.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant