

9.5 x 11.2mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#31-418** 10 TO 12 DAYS

-

1

+

₹1,305.00

ADD TO CART

Qty 1-5
₹1,305.00
Qty 6+
₹1,044.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm):

9.5 x 11.2 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 1.20
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 11.20
Width (mm): 9.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant