

TECHSPEC® 980nm, 50mm Diameter, Raman Edge Filter



Stock #86-265 10 TO 12 DAYS

- 1 + **₹177,045.00**

ADD TO CART

Qty 1-9
₹177,045.00
Qty 10+
₹147,465.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm):

989.80
Design Wavelength DWL (nm): 980
Substrate: ☐ Fused Silica (Coming 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 770 - 980
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <9.8
Clear Aperture (%): >80
Durability: Environmental: ML-STD-810F Physical: ML-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >1000
Coating Specification: T _{avg} ≥93% @ 992.7 - 2000nm
Wavelength Range (nm): 770 - 2000
Laser Blocking Wavelength (nm): 980.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View