

TECHSPEC® 9mm Dia. x 18mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock **#45-868-INK** 17 TO 22 D= DAYS

- 1 + **₹4,611.00**

ADD TO CART

Qty 1-9	₹4,611.00
Qty 10+	₹4,154.00
Volume Pricing	Request Quote

Get Product Downloads



Diameter (mm):
9.00

Back Focal Length BFL (mm):
17.12

Effective Focal Length EFL (mm): 18.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: 
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.47
Radius R₁=R₂ (mm): 18.15
Clear Aperture CA (mm): 8.1
f/#: 2.00
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View