

TECHSPEC® 9mm Dia. x -12mm FL, Uncoated, Double-Concave Lens



Stock **#48-933** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹2,480.00**

ADD TO CART

Qty 1-9
₹2,480.00
Qty 10+
₹2,240.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-12.00

Substrate: N-SF11
f/#: 1.33
Numerical Aperture NA: 0.38
Coating: Uncoated
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -12.41
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 8.1
Edge Thickness ET (mm): 2.43
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -19.16
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View