

Power Supply, 24V 10A US



Stock **#73-977** NEW **2 In Stock**

-

1

+

₹21,750

ADD TO CART

Volume Pricing	
Qty 1+	₹21,750 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Manufacturer: ProPhotonix

Hardware & Interface Connectivity

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Intensities up to 3140kLux
- 100, 300, or 600mm Length Options Available
- White, Red, Multispectral, and SWIR Illumination Options Available

ProPhotonix COBRA™ MAX LED Line Lights are slim, compact LED line lights available in lengths of 100, 300, or 600mm in red, white, multispectral, or SWIR illumination options. These line lights feature Chip-on-Board LED technology which offers greater uniformity, thermal performance, and intensity while maintaining a compact size compared to traditional surface mount LED constructions. ProPhotonix COBRA™ MAX LED Line Lights multispectral option offers RGB-IR illumination and the ability to control each wavelength independently. The available easy-to-use comprehensive software package can be customized to meet specific application needs and is downloadable from a QR code included with the units. These lights are ideal for many linescan inspection applications such as solar cell inspection, semiconductor inspection, food sorting, and flat panel display inspection.

Note: Required 24V Power Supply, [#73-977](#), sold separately. Optional Lens Kits are available to adjust the working distance by changing the position of the projection lens.