

[See all 3 Products in Family](#)

Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock #32-306 **CLEARANCE** 7 In Stock

1 MRP ₹1,362

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,362 each
Need More?	Request Quote

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

2.30 **Center Thickness CT 1 (mm):**

0.90 **Center Thickness CT 2 (mm):**

6.250000000 +0.00/-0.05 **Diameter (mm):**

Edge Thickness ET (mm):

2.86

Center Thickness Tolerance (mm):

±0.1

Centering (arcmin):

1.00

Optical Properties

Back Focal Length BFL (mm):

33.59

Coating:

Uncoated

Effective Focal Length EFL (mm):

35.0000000000

Substrate:

[N-BK7 / N-SF5](#)

Numerical Aperture NA:

0.0800000000

Radius R₁ (mm):

23.1400000000

Radius R₂ (mm):

-14.51

Radius R₃ (mm):

-38.86

Surface Quality:

40-20

Focal Length Tolerance (%):

±2

Focal Length Specification Wavelength (nm):

632.8

f#:

5.6

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photonics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

Compatible Mounts