

Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock #32-306 **CLEARANCE** 11 In Stock

− 1 + ₹1,040

ADD TO CART

Volume Pricing

Qty 1+	₹1,040 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Achromatic Lens **Type:**

#Max Edge Thickness of Curved Optic (mm):
3.860000000

#Min Edge Thickness of Curved Optic (mm):
2.360000000

Physical & Mechanical Properties

2.30 Center Thickness CT 1 (mm):

0.90 Center Thickness CT 2 (mm):

6.2500000000 +0.00/-0.05 Diameter (mm):

2.86 Edge Thickness ET (mm):

±0.1 Center Thickness Tolerance (mm):

1.00 Centering (arcmin):

Optical Properties

33.59 Back Focal Length BFL (mm):

Uncoated Coating:

35.0000000000 Effective Focal Length EFL (mm):

[N-BK7 / N-SF5](#) Substrate:

0.08 Numerical Aperture NA:

23.1400000000 Radius R₁ (mm):

-14.51 Radius R₂ (mm):

-38.86 Radius R₃ (mm):

40-20 Surface Quality:

±2 Focal Length Tolerance (%):

632.8 Focal Length Specification Wavelength (nm):

5.6 f#:

Regulatory Compliance

[View](#) Certificate of Conformance:

PRODUCT DETAILS

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photonics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

COMPATIBLE MOUNTS