

Allied Vision Alvium 1800 U-052m, 1/1.7" 0.5MP CS-Mount, Right Angle USB 3.1 Monochrome Camera

See More by [Allied Vision](#)



Stock #23-186

10 TO 12 DAYS

[Similar Cameras](#)

-

1

+

₹39,324.00

ADD TO CART

Qty 1+

₹39,324.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera
Manufacturer: Allied Vision
Mounting Threads: 1/4-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium Right Angle
Model Number: 1800 U-052m
Imaging Sensor: Sony IMX426
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.7"
Resolution (MegaPixels): 0.52
Pixels (H x V): 816 x 624
Pixel Size, H x V (µm): 9.0 x 9.0
Sensing Area, H x V (mm): 7.3 × 5.6
Frame Rate (fps): 691.00
Pixel Depth: 8/10/12 bit
Exposure Time: 21µs - 10s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 4.00
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 32 x 29 x 33 (includes connectors and lens mount)
Weight (g): 70
Mount: CS-Mount
Housing: Full
Interface Port Orientation: Back Panel (Right Angle)
Dynamic Range (dB): Not Specified
Operating Temperature (°C): +5 to +65
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

