

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Allied Vision Alvium USB 3.1 Cameras](#)

[See all 138 Products in Family](#)

Allied Vision Alvium 1800 U-291c, 2/3" 2.9MP C-Mount, USB 3.1 Color Camera

See More by [Allied Vision](#)



Allied Vision Alvium USB 3.1 Cameras



Stock **#23-167** [CONTACT US](#)

[Similar Cameras](#)



1



₹70,383.00

ADD TO CART

Qty 1+

₹70,383.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type:
Color Camera

Manufacturer:
Allied Vision

Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium
Model Number: 1800 U-291c
Imaging Sensor: Sony IMX421
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 2.91
Pixels (H x V): 1,944 x 1,472
Pixel Size, H x V (µm): 4.5 x 4.5
Sensing Area, H x V (mm): 8.8 × 6.6
Frame Rate (fps): 144.00
Pixel Depth: 8/10/12 bit
Exposure Time: 16µs - 10s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 4.00
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 38 x 29 x 29 (includes connectors and lens mount)
Weight (g): 65
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant