

Allied Vision Alvium G1-240c, 1/2.3" 2.4MP S-Mount, GigE PoE Color Camera

See More by [Allied Vision](#)



Stock **#23-546** 10 TO 12 DAYS

[Similar Cameras](#)

- 1 +

₹46,632.00

ADD TO CART

Qty 1+
₹46,632.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer:

Allied Vision
Mounting Threads: ¼"-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 32MB
Camera Family: Alvium G1
Model Number: Alvium G1-240c
Imaging Sensor: Sony IMX392
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/2.3"
Resolution (MegaPixels): 2.40
Pixels (H x V): 1,936 x 1,216
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 6.7 x 4.2
Frame Rate (fps): 49.00
Pixel Depth: 8/10/12 Bit
Exposure Time: 46µs - 10s
Connector: GigE, RJ45 with Screw Locks
Power Supply: PoE, 12 to 24 VDC via GPIO, or with external power supply #23-581
Power Consumption (W): External power: 3.6 W at 12 VDC Power over Ethernet: 4.0 W
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 36 x 29 x 29
Weight (g): 65
Mount: M12 x 0.5 (S-Mount)
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): -20 to +50
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 10-pin TFM
Machine Vision Standard: GigE Vision V1.2, GenICam V2.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

