

[See all 59 Products in Family](#)

Basler ace acA2000-165um Monochrome USB 3.0 Camera

See More by [Basler](#)



Basler ace USB 3.0 Cameras (Front)



Stock **#89-987** **1 In Stock**

[Similar Cameras](#)

-

1

+

₹1,50,500

ADD TO CART

Volume Pricing	
Qty 1+	₹1,50,500 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

acA2000-165um	Model Number:
Basler	Manufacturer:
ace	Camera Series:

Physical & Mechanical Properties

29.3 x 29 x 29 (excludes connectors and lens mount)	Dimensions (mm):
80	Weight (g):

Full	Housing:
------	----------

Sensor

Not Specified	Image Buffer:
2/3"	Sensor Format:
2.20	Resolution (Megapixels):
165.00	Frame Rate (fps):
2,048 x 1,088	Pixels (H x V):
5.5 x 5.5	Pixel Size, H x V (µm):
11.26 x 5.98	Sensing Area, H x V (mm):
CMOSIS CMV2000	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
10/12 bit	Pixel Depth:
Freely Programmable	Exposure Time:
56.5	Dynamic Range (dB):
USB3 Vision v1.0	Machine Vision Standard:

Electrical

3.2	Power Consumption (W):
-----	------------------------

Hardware & Interface Connectivity

USB 3.0	Interface:
USB 3.0, Micro-B with Screw Locks	Connector:
Power over USB	Power Supply:
1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO) or Free-Run	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:
Software Driver: Windows 32 and 64 bit, Linux, OS X	Operating System:

Threading & Mounting

C-Mount	Mount:
¼-20 with Tripod Mount Adapter #88-517	Mounting Threads:

Environmental & Durability Factors


0 to +50	Operating Temperature (°C):
-20 to +80	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Speed USB 3.0 Interface
- Ultra-Small Form Factor
- Fully USB3 Vision Compliant

Basler ace USB 3.0 Cameras are an ideal choice for analog camera users looking to upgrade to digital, or for FireWire or USB 2.0 users looking for faster data transfer rates. Basler ace USB 3.0 Cameras are fully USB3 Vision compliant and feature a small, 29 x29mm form factor that makes them easy drop-in replacements for many analog, FireWire, or USB 2.0 cameras. Additionally, these USB 3.0 cameras feature screw-locking USB 3.0 ports for increased ruggedness in demanding applications, such as factory floor use. All cameras include the Basler Pylon SDK software and driver.

Technical Information



MT9P031 Sensor QE Curve